


Ceramic, Commercial Grade, CA064, 0.01 uF, 10%, 25 V, 0612, X7R, SMD, MLCC, Array, Temp Stable, Class II



Dimensions	
L	1.6mm +/-0.2mm
W	3.2mm +/-0.2mm
T	0.8mm +/-0.1mm
P	0.8mm +/-0.1mm

Packaging Specifications	
Packaging:	T&R, 180mm, Plastic Tape
Packaging Quantity:	4000

General Information	
Style:	SMD Array
Series:	CA064
Chip Size:	0612
Description:	SMD, MLCC, Array, Temp Stable, Class II
RoHS:	Yes
Termination:	Tin
Failure Rate:	N/A

Specifications	
Capacitance:	0.01 uF
Capacitance Tolerance:	10%
Voltage DC:	25 VDC
Temperature Coefficient:	X7R