


KEMET Part Number: EFA(003)-240X240T0800
 (UFSEFA003AT080, EFA(003)240X240T0800)

Flex Suppressors, Commercial Grade, EFA



General Information	
Style:	Sheet
Brand:	NEC-Tokin
Series:	EFA
Description:	Flex Suppressor Halogen Free Type
Features:	Flame Retardant Type, Red Phosphorus Free Type
RoHS:	Yes
Approvals:	UL94 V-0, UL File No. E176124
Environment:	Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
Sheet Size	240x240mm
T	0.03mm +0.015/-0.005mm

Packaging Specifications	
Tape Description:	Without PET Tape (Txx00)
Tape Thickness:	.03mm

Specifications	
Temperature Range:	-40/+105C
Magnetic Permeability:	60 TYP At 3MHz
Effective Frequency:	10 GHz MAX
Resistance:	1 MOhms MIN
Specific Gravity:	3.1 Atm TYP
Conductivity:	1.3 W/m K
Tensile Strength:	6.8 MPa MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.