


**KEMET Part Number: EFA(005)-240X240T0800**  
 (UFSEFA005AT080, EFA(005)240X240T0800)

Flex Suppressors, Commercial Grade, EFA



#### General Information

|                     |  |
|---------------------|--|
| <b>Style:</b>       | Sheet  |
| <b>Brand:</b>       | NEC-Tokin  |
| <b>Series:</b>      | EFA  |
| <b>Description:</b> | Flex Suppressor Halogen Free Type                      |
| <b>Features:</b>    | Flame Retardant Type, Red Phosphorus Free Type         |
| <b>RoHS:</b>        | Yes  |
| <b>Approvals:</b>   | UL94 V-0, UL File No. E176124                          |
| <b>Environment:</b> | Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

#### Dimensions

|                   |                   |
|-------------------|-------------------|
| <b>Sheet Size</b> | 240x240mm         |
| <b>T</b>          | 0.05mm +/-0.015mm |

#### Packaging Specifications

|                          |                          |
|--------------------------|--------------------------|
| <b>Tape Description:</b> | Without PET Tape (Txx00) |
| <b>Tape Thickness:</b>   | .03mm                    |

#### Specifications

|                               |                |
|-------------------------------|----------------|
| <b>Temperature Range:</b>     | -40/+105C      |
| <b>Magnetic Permeability:</b> | 60 TYP At 3MHz |
| <b>Effective Frequency:</b>   | 10 GHz MAX     |
| <b>Resistance:</b>            | 1 MOhms MIN    |
| <b>Specific Gravity:</b>      | 3.1 Atm TYP    |
| <b>Conductivity:</b>          | 1.3 W/m K      |
| <b>Tensile Strength:</b>      | 6.8 MPa MIN    |