


KEMET Part Number: EFA(03)-240X240
 (UFSEFA030AT000, EFA(03)240X240)

Flex Suppressors, Commercial Grade, EFA



General Information

Style:	Sheet
Brand:	NEC-Tokin
Series:	EFA
Description:	Flex Suppressor Halogen Free Type
Features:	Flame Retardant Type, Red Phosphorus Free Type
RoHS:	Yes
Approvals:	UL94 V-0, UL File No. E176124
Environment:	Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions

Sheet Size	240x240mm
T	0.3mm +0.1/-0.05mm

Packaging Specifications

Tape Description:	No Adhesive Tape
--------------------------	------------------

Specifications

Temperature Range:	-40/+105C
Magnetic Permeability:	60 TYP At 3MHz
Effective Frequency:	10 GHz MAX
Resistance:	1 MOhms MIN
Specific Gravity:	3.1 Atm TYP
Conductivity:	1.3 W/m K
Tensile Strength:	6.8 MPa MIN