


KEMET Part Number: EFH(01)-240X240T2200
 (UFSEFH010AT220, EFH(01)240X240T2200)

Flex Suppressors, Commercial Grade, EFH



| General Information | |
|---------------------|--|
| Style: | Sheet |
| Brand: | NEC-Tokin |
| Series: | EFH |
| Description: | Flex Suppressor For High Temp, Reflow |
| Features: | High Temperature Reflow |
| RoHS: | Yes |
| Approvals: | UL94 V-0, UL File No. E176124 |
| Environment: | Halogen Free, PVC Free, Lead Free, Red Phosphorus Free |

| Dimensions | |
|------------|-----------------|
| Sheet Size | 240x240mm |
| T | 0.1mm +/-0.03mm |

| Specifications | |
|------------------------|----------------|
| Temperature Range: | -40/+105C |
| Magnetic Permeability: | 60 TYP At 3MHz |
| Effective Frequency: | 10 GHz MAX |
| Resistance: | 0.1 MOhms MIN |
| Specific Gravity: | 3.1 Atm TYP |
| Conductivity: | 1.3 W/m K |
| Tensile Strength: | 6.8 MPa MIN |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Tape Description: | Without PET Tape (Txx00) |
| Tape Thickness: | .05mm |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.