

KEMET Part Number: R75QW41504000J
(75QW41504000J)

Film, Metallized Polypropylene, Commercial Grade, R75, 1.5 uF, 5%, 1,000 V, 85C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	32mm +0.1mm
T	19mm +0.3mm
S	37.5mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	96

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R75
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C

Specifications

Capacitance:	1.5 uF
Capacitance Tolerance:	5%
Voltage DC:	1000 VDC
Voltage AC:	250 VAC
Temperature Range:	-55/+105C
Rated Temperature:	85C
Dissipation Factor:	0.06% 1kHz
Insulation Resistance:	20 GOhms
Max dVdt:	150 V
Inductance:	20 nH