

Film, Metallized Polypropylene, Safety, R41, 1 uF, 20%, 1,000 V, 300 V, 110C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3mm
H	40mm +0.1mm
T	20mm +0.3mm
S	37.5mm +/-0.4mm
LL	30mm +5/-0mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	84

General Information

Dielectric:	Metallized Polypropylene
Style:	Radial
Series:	R41
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Approvals:	ENEC, UL, cUL, CQC

Specifications

Capacitance:	1 uF
Capacitance Tolerance:	20%
Voltage DC:	1000 VDC
Voltage AC:	300 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	0.3% 1kHz
Insulation Resistance:	30 GOhms
Max dVdt:	300 V
Safety Class:	X1/Y2