

KEMET Part Number: C0603X472K5RACTU
(C0603X472K5RAC7867)

Ceramic, FlexTerm-(CxxxxX), 4700 pF, 10%, 50 V, 0603, X7R, SMD, MLCC, FT-CAP, Temperature Stable



| Dimensions | |
|------------|------------------|
| L | 1.6mm +/-0.17mm |
| W | 0.8mm +/-0.15mm |
| T | 0.8mm +/-0.15mm |
| S | 0.58mm MIN |
| B | 0.45mm +/-0.15mm |

| Packaging Specifications | |
|--------------------------|------------------------|
| Packaging: | T&R, 180mm, Paper Tape |
| Packaging Quantity: | 4000 |

| General Information | |
|---------------------|--|
| Style: | SMD Chip |
| Series: | FlexTerm-(CxxxxX) |
| Chip Size: | 0603 |
| Description: | SMD, MLCC, FT-CAP, Temperature Stable |
| Features: | FT-CAP, Temperature Stable |
| RoHS: | Yes |
| Termination: | Flexible Termination |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |

| Specifications | |
|--------------------------|---------------------|
| Capacitance: | 4700 pF |
| Capacitance Tolerance: | 10% |
| Voltage DC: | 50 VDC |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.5% |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |
| Dielectric Strength: | 125 V |