

Audio

Number of Speakers:	2
Speakers:	Yes

Basic

Adjustable Display Angle:	Yes
Aspect Ratio:	16:9
Backlight Technology:	LED
Brand Name:	BenQ
Brightness:	250 cd/m ²
Built-in Devices:	Speaker
Colour Support:	16.7 Million Colours
Colour:	Glossy Black
Contrast Ratio:	1,000:1
DVI:	Yes
Energy Star:	Yes
Environmental Certification:	ENERGY STAR 5.1
Environmentally Friendly:	Yes
HDCP Supported:	Yes
HDMI:	Yes
Maximum Resolution:	1920 x 1080
Mount Type:	Wall Mountable
Number of Screens:	1
Product Family:	GL60
Product Type:	LCD Monitor
Response Time:	2 ms
Screen Mode:	Full HD
Screen Size:	61 cm (24")
Speakers:	Yes
VESA Mount Compatible:	Yes
VGA:	Yes

Built-in Devices

Built-in Devices:	Speaker
-------------------	---------

General Information

Brand Name:	BenQ
Manufacturer Part Number:	9H.LA7LB.QBE
Manufacturer Website Address:	http://www.benq.co.uk
Manufacturer:	BenQ Corporation
Product Model:	GL2460HM
Product Name:	GL2460HM Widescreen Monitor
Product Series:	GL60
Product Type:	LCD Monitor

Interfaces/Ports

DVI:	Yes
HDMI:	Yes
Headphone:	Yes
VGA:	Yes

Miscellaneous

Energy Star:	Yes
Environmental Certification:	ENERGY STAR 5.1
Environmentally Friendly:	Yes
Platform Supported:	PC

Physical Characteristics

Colour:	Glossy Black
Depth:	194 mm
Height:	434 mm
VESA Mount Compatible:	Yes
VESA Mount Standard:	100 x 100
Weight (Approximate):	4.30 kg
Width:	565 mm

Power Description

Input Voltage:	110 V AC
Operating Power Consumption:	23 W
Standby Power Consumption:	300 mW

Technical Information

Adjustable Display Angle:	Yes
Aspect Ratio:	16:9

Backlight Technology:	LED
Features:	Senseye 3
HDCP Supported:	Yes
Horizontal Viewing Angle:	170°
Mount Type:	Wall Mountable
Number of Screens:	1
Response Time:	2 ms
Screen Mode:	Full HD
Screen Size:	61 cm (24")
Vertical Viewing Angle:	160°

Video

Brightness:	250 cd/m ²
Colour Support:	16.7 Million Colours
Contrast Ratio:	1,000:1
Maximum Resolution:	1920 x 1080