

Select Wallmount Cabinets

The economical way to
keep equipment safe.



FEATURES

- » Key lock for security.
- » Weight capacity of 50 pounds.
- » Solid welded construction.
- » Includes top-mount, low-noise fan for ventilation.
- » Powder black finish
- » Clear acrylic window enables you to view indicators.
- » Side cable knockouts.
- » Standard 19" M6 rails.

85-CFM, top-mounted fan for air movement



Top and bottom venting holes provide adequate ventilation

Clear acrylic window

Key lock for security

Side and bottom cable knockouts

TECH SPECS

Capacity — 50 lb. (22.7 kg)
Interior Height — RM2411A: 10.5" (26.7 cm);
 RM2412A: 14" (35.6 cm);
 RM2413A: 17.5" (44.5 cm)
Exterior Height — RM2411A: 13" (33 cm);
 RM2412A: 16.5" (41.9 cm);
 RM2413A: 20" (50.8 cm)
Interior Width — 18.3" (46.5 cm)
Exterior Width — 22" (55.9 cm)
Interior Depth — 22.6" (57.4 cm)
Exterior Depth — 23.6" (59.9 cm)
Weight — RM2411A: 41 lb. (18.6 kg);
 RM2412A: 46 lb. (20.9 kg);
 RM2413A: 50 lb. (22.7 kg)

What's included

- ◆ (1) Select Wallmount Cabinet
- ◆ (1) Bag of keys
- ◆ (1) Bag of screws with clear washers
- ◆ (1) Bag of M6 clip nuts
- ◆ (2) Eight inch pieces of trim

Item

Code

Select Wallmount Cabinets

6U
8U
10U

RM2411A
RM2412A
RM2413A