

Film, Metallized Polypropylene, DC Link, C4AE, 10 uF, 5%, 600 V, 70C, Lead Spacing = 27.5mm



**Dimensions**

L	31.5mm +0.5mm
H	29mm +0.2mm
T	19mm +0.3mm
S	27.5mm +/-0.4mm
LL	6mm -2mm
F	0.8mm NOM
G	0.5mm NOM

**Packaging Specifications**

<b>Packaging:</b>	Bulk
-------------------	------

**General Information**

<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Series:</b>	C4AE
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Miscellaneous:</b>	Thermal Resistance = 44 C/W

**Specifications**

<b>Capacitance:</b>	10 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage DC:</b>	600 VDC
<b>Temperature Range:</b>	-40/+85C
<b>Rated Temperature:</b>	70C
<b>Max dVdt:</b>	17 V
<b>Resistance:</b>	6.8 mOhms (10kHz 70C)
<b>Current:</b>	8.5 Amps (10kHz 70C), 169 Amps (Peak)
<b>Inductance:</b>	26 nH