


The Labgear LHG range of High Gain aerials represent the best in aerial design and construction. Easier to assemble, robust and delivering a better quality signal



NEW
Reflector Bracket



- T-match director elements and dipole provide a better balance of signals across the whole frequency range
- Massive reflector improves directivity to achieve a cleaner signal and better signal-to-noise ratio
- New twist-n-click reflector bracket speeds assembly
- Tilting mast clamp for accurate alignment
- Secure F-type connection to your cable ensures good signal transfer
- Tuned to Group T, Ch: 21-60, Freq. 460-790MHz

LHG aerials are supplied in an individual box with tilting mast clamp, f-connector, rubber weather boot and installation guide. For improved stability the larger LHG10T is supplied with a centre bracket.

Specifications	LHG5T	LHG10T
Frequency Range	470-790MHz	470-790MHz
TV Channels	21-60	21-60
Forward Gain dBi	13.9dBi	15dBi
Front to Back Ratio	>15dB	>16dB
Beam Width +/- deg.	+/-16°	+/-14°
Connector	F-Type	F-Type
Length	810mm	1440mm
Width	530mm	530mm
Width	610mm	610mm