

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0391002006](#)  
**Status:** **Active**  
**Overview:** Eurostyle™ Two-Screw Barrier Strips  
**Description:** 10.00mm Pitch Beau™ Eurostyle™ Two-Screw Terminal Strips, 6 Circuits

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                |   |
|----------------|---|
| Product Family | Terminal Blocks                                     |
| Series         | 39100   |
| Application    | Wire-to-Wire  |
| Component Type | One Piece   |
| Overview       | <a href="#">Eurostyle™ Two-Screw Barrier Strips</a> |
| Product Name   | Eurostyle™ Two Screw                                |
| Type           | Barrier Strip                                       |
| UPC            | 78172545155   |

**Physical**

|                               |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 6                              |
| Circuits (maximum)            | 6                              |
| Color - Resin                 | White                          |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | None                           |
| Material - Metal              | Stainless Steel                |
| Material - Resin              | Nylon                          |
| Number of Rows                | 2                              |
| Orientation                   | Vertical                       |
| PCB Retention                 | Yes                            |
| Panel Mount                   | Mounting Holes Between Circuit |
| Pitch - Mating Interface      | 10.00mm                        |
| Pitch - Termination Interface | 10.00mm                        |
| Polarized to Mating Part      | No                             |
| Stackable                     | No                             |
| Temperature Range - Operating | -40°C to +105°C                |
| Wire Size AWG                 | 10, 12, 14, 16, 18             |

**Electrical**


|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 30.0A |
| Voltage - Maximum             | 600V  |

**Material Info**

|                 |                 |
|-----------------|-----------------|
| Old Part Number | M800-02-06-5-M1 |
|-----------------|-----------------|

**Reference - Drawing Numbers**

|               |              |
|---------------|--------------|
| Sales Drawing | SD-39100-013 |
|---------------|--------------|



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/108/2014 (17 Dec 2014)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

**Search Parts in this Series**

[39100 Series](#)