

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150150427](#)
Status: **Active**
Overview: Premo-Flex™ Cable Jumpers
Description: 0.30mm Pitch Premo-Flex™ Etched Polyimide Jumper, Same Side Contacts (Type A), 0.102m Cable Length, 0.12mm Cable Thickness, 27 Circuits

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	15015
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ Cable Jumpers
Product Name	Premo-Flex™FFC Jumper
UPC	884982822542

Physical

Cable Length	0.102m
Circuits (Loaded)	27
Circuits (maximum)	27
Net Weight	1.000/g
Packaging Type	Bag
Pitch - Termination Interface	0.30mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable


Electrical

Current - Maximum per Contact	0.2A
Voltage - Maximum	50V AC/DC

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-15015-001, SD-15021-015, SD-15021-024, SD-15021-033, SD-15022-030, SD-15022-050, SD-15022-080, SD-15023-041, SD-15023-051
---------------	--



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series
[15015 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION