

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1703520002](#)
Status: **Active**
Description: EXTreme Guardian™ 2 Circuit TPA

Documents:

[3D Model](#) [Product Specification PS-46819-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Housings
 Series [170352](#)
 Application Wire-to-Board, Wire-to-Wire
 Product Name EXTreme Guardian™
 UPC 884982274457


Physical

Circuits (maximum) 0
 Color - Resin Black
 Gender N/A
 Glow-Wire Compliant No
 Keying to Mating Part None
 Material - Resin Polyester
 Net Weight 1.750/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount N/A
 Pitch - Mating Interface N/A
 Temperature Range - Operating -40°C to +105°C

Material Info

Reference - Drawing Numbers

Product Specification PS-46819-001
 Sales Drawing SD-170352-0002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

China RoHS

Green Image
 Not Relevant

Search Parts in this Series

[170352](#) Series

Use With

[170351](#) EXTreme Guardian™ Crimp
 Harness Housing