

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010084](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect® Crimp Contact Insert, Male, 8-Pole, 10A, for Turned or Stamped Crimp Contacts, Size 3A «21x21»](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	3A «21x21»
Component Type	Inserts - Crimp Contact
Insert Series	S-D8
Mates With	93601-0081 Female Crimp Contact Insert
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect®
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191869520
Use With	Turned or Stamped Contacts - Male

Physical

Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Number of Rows	3
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	50V

Material Info

Old Part Number	7108.4102.0
-----------------	-------------

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[93601](#) Series