

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0368760001](#)
Status: **Active**
Overview: [Ditto™ Wire-to-Wire Interconnects](#)
Description: [Ditto™ Genderless Crimp Terminal, High Copper, Tin Plating, 20-22 AWG](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	36876
Application	Power
Crimp Quality Equipment	Yes
Overview	Ditto™ Wire-to-Wire Interconnects
Product Name	Ditto™
UPC	887191582801

Physical

Durability (mating cycles max)	25
Gender	Genderless
Material - Metal	High Copper
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Net Weight	0.148/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.70mm
Wire Size AWG	20, 22
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	26.0A
Voltage - Maximum	350V AC/DC

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[36876 Series](#)

Use With

[Ditto™ Genderless Crimp Housing 36877](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Manual Extraction Tool	0638131400
Hand Crimp Tool For Ditto™ Crimp Terminals	0638273400
FineAdjust™ Applicator for Ditto™	0639030200

This document was generated on 07/15/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION