


COMMUNICATION & CONTROL MULTIPAIR, FOIL SHIELD PVC/PVC

UL TYPE CM
UL AWM 2464, CSA PCC FT4
300 VOLT



CHARACTERISTICS

Operating Temperature:

- -20°C to 80°C - AWM
- 75°C - CM

Voltage Rating:

- 300 Volt

Color Description:

- Color Code: Chart K [Page 368](#)
*Chart C [Page 365](#)
- Jacket Color: Gray

Product Description:

- Conductor: Stranded Tinned Copper
- Insulation: Color-Coded PVC
- Shield: Aluminum/Polyester Tape
Foil Facing Inward (100% Coverage)
- Drain Wire: Stranded Tinned Copper
- Jacket: PVC

SPECIFICATIONS

- UL Type CM, AWM 2464
- CSA PCC FT4
- Passes UL Vertical Tray Flame Test
- "C" Suffix Indicates CM Rating



AVAILABILITY

- 100 ft (30,5m), 500 ft (152m), 1000 ft (305m) put-ups

80°C 300V PVC - UL 2464 - TYPE CM

24 AWG (0,23mm²), **7/32** (7x0,20mm), Insulation Thickness: **0.010"** (0,25mm)

Alpha Part No.	No. of Pairs	Jacket Thickness		Diameter		Drain Wire	
		In.	mm	In.	mm	AWG	Strand
5471C	1	0.032	0,81	0.16	4,1	0.24	7/32
5472C	2	0.032	0,81	0.21	5,3	0.24	7/32
5473C	3	0.032	0,81	0.23	5,8	0.24	7/32
5474C	4	0.032	0,81	0.24	6,1	0.24	7/32
5475C	5	0.035	0,89	0.27	6,9	0.24	7/32
5476C	6	0.035	0,89	0.30	7,6	0.24	7/32
5477C	7	0.035	0,89	0.30	7,6	0.24	7/32
5478C	8	0.035	0,89	0.32	8,1	0.24	7/32
5479C	9	0.037	0,94	0.34	8,6	0.24	7/32
5480C	10	0.040	1,02	0.38	9,6	0.24	7/32
5480/15C	15	0.040	1,02	0.42	10,8	0.24	7/32
5480/19C	19	0.040	1,02	0.45	11,4	0.24	7/32
5480/25C	25	0.045	1,14	0.53	13,4	0.24	7/32
5480/50C*	50	0.053	1,35	0.70	17,8	0.24	7/32

See page 198 for 22 AWG product.

Tel: 908-925-8000
Toll-Free: 1-800-52 ALPHA
Fax: 908-925-6923

IN EUROPE:
Tel: +44 01932 772422
Fax: +44 01932 772433

Master Catalog Page



197



Communication and Control Product Section Index



Who is Alpha - Online Catalog - Product Info/Search - Technical Info
Marketing & Media - Ordering Info - Contact Us - Distributor Locator - Site Map

Copyright © 1998 Alpha Wire Company. All rights reserved.