

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347910040](#)
Status: **Active**
Overview: [Mini50™ Connection Systems](#)
Description: Mini50™ Unsealed Receptacle, Single Row, Non-Bridged, 4 Circuits, Polarization Option A, Black

Documents:

[3D Model](#) [Packaging Specification PK-31301-538 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-34791-020 \(PDF\)](#)

General

Product Family Crimp Housings
Series [34791](#)
Application Power, Wire-to-Board
Overview [Mini50™ Connection Systems](#)
Polarization A
Product Name Mini50™
UPC 884982491434

Physical

Circuits (maximum) 4
Color - Resin Black
Gender Receptacle
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin PBT
Net Weight 0.800/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.00mm
Pitch - Termination Interface 2.00mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Reference - Drawing Numbers

Application Specification AS-34791-020
Packaging Specification PK-31301-538
Sales Drawing SD-34791-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Compliant

Search Parts in this Series

[34791 Series](#)

Mates With

Mini50™ Vertical Header [34792](#) , Mini50™ Right-Angle Through Hole Header [34793](#) , Mini50™ Right-Angle Surface Mount Header [34912](#)

Use With

CTX50 Unsealed Terminals [560023](#)