

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0367921201](#)  
**Status:** **Active**  
**Overview:** MX120G&#153 Sealed Connectors  
**Description:** MX120G™ Pitch Sealed Female Connector Assembly, Dual Row 12 Circuit, Black

**Documents:**

[3D Model](#) [Packaging Specification PK-36783-002 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [36792](#)  
 Application Wire-to-Board  
 Overview [MX120G&#153 Sealed Connectors](#)  
 Product Name MX120G™  
 UPC 887191146799

**Physical**

Circuits (maximum) 12  
 Color - Resin Black  
 Flammability 94HB  
 Gender Female  
 Glow-Wire Compliant No  
 Keying to Mating Part N/A  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 11.279/g  
 Number of Rows 2  
 Packaging Type Carton  
 Panel Mount No  
 Pitch - Mating Interface 3.20mm  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating -40°C to +105°C

**Electrical**

Current - Maximum per Contact 10.5A


**Solder Process Data**

Lead-free Process Capability N/A

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-36783-002  
 Sales Drawing SD-36792-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

**Search Parts in this Series**

[36792 Series](#)

**Use With**