

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **[1301080083](#)**  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway™ 15W Fluorescent Hand Lamp With Handle Ballast Location and Switch, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR85374  
UL E59049

**General**

Product Family Portable Lighting  
Series [130108](#)  
NEMA Configuration NEMA 5-15  
Outlet None  
Overview [Hand Lamps](#)  
Product Literature Order No 987650-8053  
Product Name Super-Safeway™  
Type Hand Lamps  
UPC 78678861245  
Woodhead Yes

**Physical**

Cord Length - Primary 15.24m (50.0')  
Cord Length - Secondary N/A  
Depth 58.40mm (2.300")  
Duty Industrial  
Guard Included No  
Guard Type N/A  
Height N/A  
Length 411.73mm (16.210")  
Material - Globe Butyrate  
Material - Guard Nitrile Rubber 80 Shore A  
Mounting Style Hand Held  
Packaging Type Carton  
Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
Cord Type - Primary 18/3 SJTW  
Lamp Type F15/T8  
Lamp Wattage - Maximum 15W  
Lumens 910  
On/Off Switch Yes  
Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 1005-3



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed  
ELV Not Reviewed  
RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130108 Series](#)