

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1805800005](#)
Status: **Active**
Overview: LED Array Holders, Dual-Ended Wire Trap
Description: LED Array Holder for 16.00 by 19.00mm COB, Circular Version, Gold (Au) Plating, One-Piece Design with Three-finger attachment for LEDiL Angela/Angelina Reflectors

Documents:

[3D Model](#) [Packaging Specification PK-180336-104 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E345583

General

Product Family Solid State Lighting
 Series [180580](#)
 Array Type Nichia*
 Beam Angle N/A
 Height 4.10mm
 Overview [LED Array Holders, Dual-Ended Wire Trap](#)
 Product Name Wire Trap Holder
 Type LED COB Array Holder
 UPC 887191461090

Physical

Base Type N/A
 Color Rendering Index (CRI) N/A
 Correlated Color Temp (CCT) N/A
 Flammability 94V-0
 Lamp Type N/A
 Mounting Style Screws
 Net Weight 8.954/g
 Packaging Type Tray

Electrical

Lamp Wattage - Maximum N/A
 Lumens N/A
 Voltage (Fixture) - Maximum 600V DC
 Wiring Style Poke In Wire Traps

Material Info

Reference - Drawing Numbers

Packaging Specification PK-180336-104
 Sales Drawing SD-180580-004

*NICHIA is a trademark of NICHIA CORPORATION



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

**Halogen-Free
 Status**

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series
[180580 Series](#)