

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0733870021](#)

**Status:** **Active**

**Overview:** Precision Compression-Mount Microwave Test Connectors

**Description:** 50 Ohms, Precision Test Connector, 2.4mm Jack Receptacle, 2 Hole Flange Mount, with 2 Screws 6.35mm, PCB Thickness 1.96-3.99mm

**Documents:**

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	RF/Coax Connectors
Series	73387
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	2.40mm
Style	PCB
UPC	884982517653
Wire/Cable Type	N/A

**Physical**

Gender	Jack
Keying to Mating Part	None
Net Weight	2.115/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	Compression
Reverse Polar	No

**Electrical**

Impedance	50#
-----------	-----


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-73387-002, SD-73387-002-PKG
---------------	--------------------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - ED/21/2016 (20 June 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

**Search Parts in this Series**

[73387](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**