

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640033**
Status: **Active**
Overview: Perma-Seal™ Terminals
Description: Perma-Seal™ Ring Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series 19164
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview Perma-Seal™ Terminals
Product Name Perma-Seal™
Type Ring
UPC 800753113213

Physical

Barrel Type Closed
Insulation NiAc™
Material - Plating Mating Tin
Net Weight 1.034/g
Packaging Type Bag
Stud Size 8 (M4)
Wire Insulation Diameter 5.97mm
Wire Size AWG 14, 16
Wire Size mm² 1.23-1.94

Material Info

Old Part Number SB-237-08

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing SD-19164-026



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

19164 Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Power Crimp Tool Head for Terminals 10-22 AWG Wire	<u>0640057400</u>
PremiumGrade™ Hand Crimp Tool	<u>0640017400</u>