

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010079](#)  
**Status:** **Active**  
**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect® Crimp Contact Insert, Male, 7-Pole, 10A, for Crimp Contacts, Size 3A «21x21», Grey](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                  |  |
|------------------|--|
| Product Family   | Industrial Connectors / Enclosures                     |
| Series           | <a href="#">93601</a>                                  |
| Component Size   | 3A «21x21»   |
| Component Type   | Inserts - Crimp Contact                                |
| Insert Series    | SD-7   |
| Mates With       | <a href="#">93601-0077</a> Female Crimp Contact Insert |
| Overview         | <a href="#">GWconnect® Heavy Duty Connectors (HDC)</a> |
| Product Category | Heavy Duty Connectors                                  |
| Product Name     | GWconnect®   |
| Standard         | CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977     |
| UPC              | 887191868875   |
| Use With         | Turned or Stamped Contacts - Male                      |

**Physical**

|                                |                 |
|--------------------------------|-----------------|
| Durability (mating cycles max) | 500             |
| Flammability                   | UL 94V-0        |
| Gender                         | Male            |
| Insert Color                   | Grey            |
| Material - Insert              | Polycarbonate   |
| Number of Rows                 | 3               |
| Packaging Type                 | Bag             |
| Polarized to Mating Part       | Yes             |
| Poles                          | 7               |
| Temperature Range - Operating  | -40°C to +125°C |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 10.0A |
| Voltage - Maximum             | 250V  |

**Material Info**

|                 |             |
|-----------------|-------------|
| Old Part Number | 7107.4101.0 |
|-----------------|-------------|

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[93601](#) Series