

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1110150100](#)  
**Status:** **Active**  
**Overview:** HSAutoLink™ Interconnect Systems  
**Description:** HSAutoLink™ Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 0.50m Length, Polarization A

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-68800-001 \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	111015
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Type A-to-Mini-B
Overview	HSAutoLink™ Interconnect Systems
Product Name	HSAutoLink™ USCAR/USB
UPC	883906510060

**Physical**

Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	38.730/g
Single Ended	No
Wire/Cable Type	Round

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-68800-001
Sales Drawing	SD-111015-006



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/108/2014 (17 Dec  
2014)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[111015 Series](#)

**Mates With**

[49616 USCAR/USB Header](#)