

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0889416100](#)  
**Status:** **Active**  
**Overview:** [Pre-Crimped Leads](#)  
**Description:** Pre-Crimped Lead Pico-SPOX™ Female-to-Pico-SPOX™ Female, 300mm, 24 AWG

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">88900</a>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-SPOX™ Crimp Terminals
Overview	<a href="#">Pre-Crimped Leads</a>
Product Name	Pico-SPOX™
UPC	884982028128

**Physical**

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.987/g
Packaging Type	Bag
Pitch - Mating Interface	1.50mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Waterproof / Dustproof	No
Wire Size AWG	24
Wire/Cable Type	UL 1007


**Electrical**

Shielded	No
----------	----

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-88941-6100
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[88900 Series](#)

**Mates With**

[87421-0000 Crimp Terminals](#)

**Use With**

[Pico-SPOX™ Housings 87439](#)