

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934447131](#)
Status: **Active**
Overview: ML-XT™ Sealed Connection System
Description: ML-XT™ Sealed 18 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Keying Option C, Black

Documents:

Drawing (PDF)	Packaging Specification 934430002 (PDF)
Product Specification 934430010 (PDF)	Packaging Specification 934430010 (PDF)
Application Specification 934430010 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	<u>ML-XT™ Sealed Connection System</u>
Product Name	ML-XT™
UPC	889056335348

Physical

Circuits (maximum)	18
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	17.440/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002, 934430010
Product Specification	934430010
Sales Drawing	934430070

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

Search Parts in this Series

[93444 Series](#)

Mates With

[ML-XT™ Sealed 18 Circuit Plug Housing 93445-7131](#)

Use With

[ML-XT™ Male \(Pin\) Terminal 84524-0004 \(Nickel\)](#), [ML-XT™ Male \(Pin\) Terminal 84524-0014 \(Selective Gold\)](#), [ML-XT™ Blind Cavity Plug 93494-1000](#)