

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0934453101](#)
Status: **Active**
Overview: [ML-XT™ Sealed Connection System](#)
Description: ML-XT™ Sealed 4 Circuit Plug Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

Drawing (PDF)	Packaging Specification 934430002 (PDF)
Product Specification 934430010 (PDF)	Packaging Specification 934430010 (PDF)
Application Specification 934430010 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	93445
Application	Power, Signal, Wire-to-Wire
Application Tooling Part Link	63824-5300
Overview	ML-XT™ Sealed Connection System
Product Name	ML-XT™
UPC	889056164542

Physical

Circuits (maximum)	4
Color - Resin	Black
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	6.674/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	934430010
Packaging Specification	934430002, 934430010
Product Specification	934430010
Sales Drawing	934430030



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[93445](#) Series

Mates With

ML-XT™ Sealed 4 Circuit Receptacle Housing [93444-3101](#)

Use With

ML-XT™ Female (Socket) Terminal [84525-0009](#) (Nickel), ML-XT™ Female (Socket) Terminal [84525-0032](#) (Selective Gold), ML-XT™ 4 Circuit Plug Wedgelock [93448](#) , ML-XT™ Blind Cavity Plug [93494-1000](#)