

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300530002](#)

Status: **Active**

Overview: Brad® Industrial Ethernet Solutions

Description: Brad® RJ-Lnxx® R-J45 110 Punchdown Ethernet Receptacle, with Hex Nut and Bulkhead Gasket, 1" - 14 UNC Threads, 0.056m (2.19") Length

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	130053
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad® Industrial Ethernet Solutions
Product Name	Brad®, RJ-Lnxx®
Type	110 Punchdown
UPC	78678846635

Physical

Coupling Type	External Thread
Gender	Female
Keyway	None
Length	0.056m
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Net Weight	24.500/kg
Orientation	Straight
Panel Mount	Front
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	125V DC

Material Info

Old Part Number	ENDR2FB5
-----------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-130053-002
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[130053 Series](#)