

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1704650002](#)
Status: **Active**
Overview: [CXP Interconnect System](#)
Description: 0.80mm Pitch, iPass+™ CXP-EF, External Application, Single-Port Integrated Cage and Connector Assembly, Right Angle, Press-Fit, 84 Circuit, 0.76µm Gold (Au) Plating

Documents:

3D Model	Application Specification AS-170465-0002 (PDF)
Drawing (PDF)	Packaging Specification PK-170465-0001 (PDF)
Application Specification AS-170465-0001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


CSA	LR19980
UL	E107635

General

Product Family	I/O Connectors
Series	170465
Application	Board-to-Board, Module-to-Board, Wire-to-Board
Comments	Maximum Current is 0.5A Per Pin
Component Type	Cage Assembly, Plug
Electrical Model	Yes
Overview	CXP Interconnect System
Product Name	iPass+™
Type	N/A
UPC	884982257757

Physical

Boot Color	N/A
Circuits (Loaded)	84
Circuits (maximum)	84
Circuits Detail	84
Durability (mating cycles max)	250
Flammability	94V-0
Gender	Female
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Nickel
Material - Plating Termination	Gold
Net Weight	30.031/g
Number of Rows	4
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	N/A
Waterproof / Dustproof	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[170465](#) Series

Mates With

[111025](#) iPass+™ Cable

Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	0.5A
Grounding to Panel	N/A
Shield Type	Full Shield
Shielded	Yes

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info**Reference - Drawing Numbers**

Application Specification	AS-170465-0001, AS-170465-0002
Electrical Model Document	EE-170465-0101
Packaging Specification	PK-170465-0001
S-Parameter Model	SP-170465-0101
Sales Drawing	SD-170465-0001

This document was generated on 08/31/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION