

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120080013](#)
Status: **Active**
Overview: [Network Diagnostics Tools](#)
Description: NetMeter® Hand Held Digital DeviceNet*

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	112008
Approvals	CE, CUL, UL certified
Comments	NetMeter®; Measures 667 Parameters
Communication Speed	125, 250, 500 Kbaud
I/O Connector	5-pole Micro-Change® (M12)
IP Rating	N/A
Overview	Network Diagnostics Tools
Product Literature Order No	987650-3281
Product Name	DeviceNet®, NetMeter®
Type	Hand Held Digital NetMeter®
UPC	78172506708

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	N/A
Material - Connector Body	N/A
Material - Contact	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC

Material Info

Old Part Number	DN-MTR
-----------------	--------

*DeviceNet is a trademark of the ODVA



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[112008 Series](#)