

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194340004](#)
Status: **Active**
Overview: [MX150L™ Industrial Sealed Connector System](#)
Description: [MX150L™ Female Terminal for 8 AWG Wire](#)

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19432-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-19434-001 (PDF)	

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Crimp Terminals
Series	19434
Application	Power
Comments	UL E152602
Crimp Quality Equipment	Yes
Overview	MX150L™ Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822350193160

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.828/g
Packaging Type	Bag
Wire Insulation Diameter	6.02mm
Wire Size AWG	8
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19434-001
Product Specification	PS-19432-001
Sales Drawing	SD-19434-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/108/2014 (17 Dec
2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19434 Series](#)

Mates With

[19431 Male Terminal](#)

Use With

[19432 Female Receptacle](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description

Product #

Hand Crimp Tool for	0638115400
Crimp Terminals	

This document was generated on 06/09/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION