

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010047](#)  
**Status:** **Active**  
**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect® Turned Crimp Contact for 10A Inserts and Modules, Female, Silver \(Ag\) Plated Copper Alloy, 1.50mm² \(16 AWG\), 100 per Bag](#)

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Contact Type	Turned Crimp Contact
Mates With	<a href="#">93601</a> Male Turned Crimp Contact
Overview	<a href="#">GWconnect® Heavy Duty Connectors (HDC)</a>
Product Category	Contacts
Product Name	GWconnect®
UPC	887191866758
Use With	S-D, S-DD, S-K, S-Q, S-QD, and S-M Inserts

**Physical**

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Number of Grooves	0
Packaging Type	Bag
Stripping Length	8.00mm
Wire Size AWG	16
Wire Size mm²	1.50


**Electrical**

Current - Maximum per Contact	10.0A
-------------------------------	-------

**Material Info**

Old Part Number	7100.4205.0
-----------------	-------------

GWconnect® is a registered trademark of Molex Incorporated in Italy and may be registered in other jurisdictions.



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[93601](#) Series