

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348406010](#)
Status: **Active**
Overview: MX150™ Sealed and Unsealed Connector System
Description: MX150™ Sealed Male Connector, Bulkhead Twist-Lock, Dual Rows, 12 Circuits, Polarization A, Black

Documents:

[3D Model](#) [Packaging Specification PK-31301-615 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|----------------|--|
| Product Family | Crimp Housings |
| Series | 34840 |
| Application | Power, Wire-to-Wire |
| Overview | <u>MX150™ Sealed and Unsealed Connector System</u> |
| Product Name | MX150™ |
| UPC | 884982569546 |


Physical

| | |
|-------------------------------|----------------------------|
| Circuits (maximum) | 12 |
| Circuits Detail | 12 |
| Color - Resin | Black, Natural |
| Gender | Male |
| Glow-Wire Compliant | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Modified Polystyrene Alloy |
| Net Weight | 24.020/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | Yes |
| Pitch - Mating Interface | 3.50mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +125°C |

Material Info

Reference - Drawing Numbers

| | |
|-------------------------|--------------|
| Packaging Specification | PK-31301-615 |
| Sales Drawing | SD-34840-001 |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Compliant

Search Parts in this Series

[34840](#) Series

Mates With

[33472](#) MX150™ Sealed Connector

Use With

[33000](#) MX150™ Male Terminal