

General Information

Extended Product Type:	PG5-R2
Product ID:	1SNK900403R0000
EAN:	3472599097353
Catalog Description:	PG5-R2 Component Plug - Dark Grey
Long Description:	- Component holder compatible with 5.2 mm 0.205 in spacing ZS4 feed-through terminal blocks, - Fit components 16 x 16 x 8.5 mm 0.630 x 0.630 x 0.335 in (not supplied with plug) such as resistors, diodes, varistance, - Direct plug-in into the terminal blocks jumper channels, - Maximum dissipatived power: 2 W.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Component Plugs

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010
Color:	Dark Grey

Dimensions

Product Net Height:	37.9 mm
Product Net Length:	48.9 mm
Product Net Depth:	48.9 mm
Product Net Weight:	8 g
Product Net Width:	10 mm

Technical

Spacing:	9.95 mm
Function:	Component Plugs
Rated Voltage (U _r):	250 V
Rated Impulse Withstand Voltage (U _{imp}):	4000 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Suitable For:	ZDP2.5-11 ZDP2.5-22 ZK2.5 ZK2.5-3P ZK2.5-4P ZK2.5-D2 ZK2.5-D-CH ZP2.5 ZP2.5-3P ZP2.5-4P ZP2.5-D2 ZS4 ZS4-D2 ZS4-D-CH ZS4-R2 ZS4-T3 ZS4-T3-R1

Technical UL/CSA

Flammability According to UL94:	V0
---------------------------------	----

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
Data Sheet, Technical Information:	1SNK160039D0201

Classifications

E-nummer:	2925159
ETIM 4:	EC002018 - Component plug terminal block
ETIM 5:	EC002018 - Component plug terminal block
ETIM 6:	EC002018 - Component plug terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	101 mm
Package Level 1 Length:	120 mm
Package Level 1 Height:	50 mm
Package Level 1 Gross Weight:	0.16 kg
Package Level 1 EAN:	3472599097353
Package Level 2 Units:	160 piece
Package Level 2 Width:	200 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	1.53 kg
Package Level 3 Units:	15360 piece
Product Packing Type:	Box
Package Level 1 Units:	20 piece

