

General Information

Extended Product Type:	ZS4-SF-T2
Product ID:	1SNK506411R0000
EAN:	3472595064113
Catalog Description:	ZS4-SF-T2 Screw Clamp Terminal Block - for Fuses 5x20mm - with 2 test socket screws DIA 2 mm .079 in
Long Description:	- Protect your circuits with 5x20 fuse terminal blocks compliant with IEC 60947-7-3 standard (fuse not supplied with the terminal blocks), - Simplify the distribution thanks to the two jumper channels aligned with ZS4 or ZS4-R2 feed-through and ZS4-S-R1 disconnect terminal blocks, - Ease the test with built-in test socket screws.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » SNK Series

Ordering

Minimum Order Quantity:	50 piece
Customs Tariff Number:	85369010
Color:	Grey, Dark Grey

Dimensions

Product Net Height:	70.5 mm
Product Net Length:	76.8 mm
Product Net Depth:	76.8 mm
Product Net Weight:	18.6 g
Product Net Width:	6 mm

Technical

Spacing:	6 mm
Connection Type:	Screw clamp
Function:	Fuse
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.22 ... 4 mm ² Screw Clamp / Flexible 2x 0.2 ... 1.5 mm ² Screw Clamp / Rigid 1x 0.2 ... 4 mm ² Screw Clamp / Rigid 2x 0.2 ... 1.5 mm ² Screw Clamp / With Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / Without Insulated Ferrule 1x 0.22 ... 4 mm ² Screw Clamp / With Twin Ferrule 2x 0.22 ... 1.5 mm ²
Gauge Type:	A3-B3
Rated Current (I_n):	Main Circuit 6.3 A
Rated Voltage (U_r):	500 V
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Dielectric Test Voltage:	1890 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	10.5 mm
Recommended Screw Driver:	3.5 mm
Rated Cross-Section:	4 mm ²

Technical UL/CSA

Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Flexible 1x 24 ... 10 AWG Screw Clamp / Flexible 2x 24 ... 16 AWG Screw Clamp / Rigid 1x 24 ... 10 AWG Screw Clamp / Rigid 2x 24 ... 16 AWG Screw Clamp / With Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / Without Insulated Ferrule 1x 24 ... 12 AWG Screw Clamp / With Twin Ferrule 2x 24 ... 16 AWG
Connecting Capacity UL/CSA:	Stranded 10 AWG
Flammability According to UL94:	V0
Maximum Operating Voltage UL/CSA:	Main Circuit 150 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

BV Certificate: 1SND161073A0203

CB Certificate: 1SND161029A0203

CSA Certificate: 1SND161070A0208

cUL Certificate: 1SND161040A0206

Data Sheet, Technical Information: 1SNK161038D0201

Declaration of Conformity - CE: 1SND225103U1000

DNV Certificate: 1SND161087A0202

EAC Certificate: 1SND161009A1100

RINA Certificate: 1SND161088A0200

RoHS Information: 1SND230491F0206

Classifications

E-nummer: 2925949

ETIM 4: EC000899 - Fuse terminal block

ETIM 5: EC000899 - Fuse terminal block

ETIM 6: EC000899 - Fuse terminal block

Object Classification Code: X

Container Information

Package Level 1 Width: 138 mm

Package Level 1 Length: 151 mm

Package Level 1 Height: 78 mm

Package Level 1 Gross Weight: 0.93 kg

Package Level 1 EAN: 3472595064113

Package Level 2 Units: 400 piece

Package Level 2 Width: 300 mm

Package Level 2 Length: 400 mm

Package Level 2 Height: 200 mm

Package Level 2 Gross Weight: 7.940 kg

Package Level 3 Units: 19200 piece

Product Packing Type: Box

Package Level 1 Units: 50 piece

