

General Information

Extended Product Type:	JB16-2
Product ID:	1SNK916302R0000
EAN:	3472599163027
Catalog Description:	JB16-2 Jumper Bar - Orange
Long Description:	Insulated jumper bar with screw mounting.

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars
--

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010
Color:	Orange

Dimensions

Product Net Height:	27.5 mm
Product Net Length:	23.4 mm
Product Net Depth:	23.4 mm
Product Net Weight:	10 g
Product Net Width:	16 mm

Technical

Spacing:	16 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 125 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 4200 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	4 W
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Recommended Screw Driver:	5.5 mm
Suitable For:	M35/16 ZS35 ZS50 ZS50-PE

Technical UL/CSA

Flammability According to UL94:	V0
Maximum Operating Voltage UL/CSA:	Main Circuit 600 V

Environmental

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
ATEX Certificate:	1SND162004A1706
CB Certificate:	1SND161028A0202
Data Sheet, Technical Information:	1SNK160032D0201
RoHS Information:	1SND230499F0202

Classifications

E-number:	2925388
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block
Object Classification Code:	X

Container Information

Package Level 1 Width:	125 mm
Package Level 1 Length:	170 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.1 kg
Package Level 1 EAN:	3472599163027
Package Level 2 Units:	1000 piece
Package Level 2 Width:	200 mm
Package Level 2 Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	48000 piece
Product Packing Type:	Bag
Package Level 1 Units:	10 piece

