

General Information

Global Commercial Alias:	ACS55-01E-04A3-2
Product ID:	68878357
ABB Type Designation:	ACS55-01E-04A3-2
EAN:	6410038784348
Catalog Description:	IP20; 1 phase

Categories

Products » Drives » Low voltage AC drives » Micro drives

Ordering

Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85044084
EAN:	6410038784348
Invoice Description:	ACS55 ACS55-01E-04A3-2 Pn 0,75kW, I2n 4,3A IP20
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Quote Only:	No
Replaced Product ID (OLD):	64759248
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU

Dimensions

Product Net Height:	146.5 mm
Product Net Length:	67.5 mm
Product Net Weight:	0.7 kg
Product Net Width:	128 mm

Technical

Enclosure Class:	IP20
Frequency (f):	48 ... 63 Hz
Input Voltage (U _{in}):	200 ... 240 V
Mounting Type:	Wall-mounted
Number of Phases:	1
Output Current, Light-Overload Use:	4.3 A
Output Current, Normal Use:	4.3 A
Output Power, Light-Overload Use:	0.75 kW 1.0 Hp
Output Power, Normal Use:	0.75 kW 1.0 Hp
Two Speed Motor:	No

Additional Information

Product Main Type:	ACS55
Product Name:	Frequency converter

Classifications

Product Series:	ACS55
-----------------	-------

