

## General Information

Global Commercial Alias:	ACS55-01E-09A8-2
Product ID:	68878373
ABB Type Designation:	ACS55-01E-09A8-2
EAN:	6410038784362
Catalog Description:	IP20; 1 phase

## Categories

Products » Drives » Low voltage AC drives » Micro drives

## Ordering

Country of Origin:	China (CN) Finland (FI)
Customs Tariff Number:	85044084
EAN:	6410038784362
Invoice Description:	ACS55 ACS55-01E-09A8-2 Pn 2,2 kW, I2n 9,8A IP20
Made To Order:	No
Minimum Order Quantity:	1 piece
Order Multiple:	1 piece
Quote Only:	No
Replaced Product ID (OLD):	<a href="#">68322111</a>
Selling Unit of Measure:	piece
Stocked At (Warehouses):	Central Stock Europe Central Stock Asia FIPSEEXPU014 SGRDC002EXPU CNIAB001EXPU SGIND002EXPU AUABB024EXPU

## Dimensions

Product Net Height:	203 mm
Product Net Length:	70 mm
Product Net Weight:	1.1 kg
Product Net Width:	159 mm

## Technical

Enclosure Class:	IP20
Frequency (f):	48 ... 63 Hz
Input Voltage (U <sub>in</sub> ):	200 ... 240 V
Mounting Type:	Wall-mounted
Number of Phases:	1
Output Current, Light-Overload Use:	9.8 A
Output Current, Normal Use:	9.8 A
Output Power, Light-Overload Use:	2.2 kW 3 Hp
Output Power, Normal Use:	2.2 kW 3 Hp
Two Speed Motor:	No

## Additional Information

Product Main Type:	ACS55
Product Name:	Frequency converter

## Classifications

Product Series:	ACS55
-----------------	-------

