

General Information

Extended Product Type:	216RS4W
Product ID:	2CMA167148R1000
EAN:	7392696671484
Catalog Description:	Surface socket-outlet, 4h, 16A, IP67, 2P+E
Long Description:	Surface socket-outlet, earthing sleeve position 4h, rated current 16A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Yellow

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Socket Outlets

Ordering

EAN:	7392696671484
Minimum Order Quantity:	1 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	99 mm
Product Net Height:	172 mm
Product Net Length:	115 mm
Product Net Depth:	172 mm
Product Net Weight:	0.34 kg

Container Information

Package Level 1 Width:	144 mm
Package Level 1 Length:	202 mm
Package Level 1 Height:	140 mm
Package Level 1 Gross Weight:	0.42 kg
Package Level 1 EAN:	7392696671484
Package Level 1 Units:	1 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	------------------------------------------------------------------------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	IP69
Cable Cross-Section:	1.5 ... 4 mm ²
Color:	Yellow
Degree of Protection:	IP67
Enclosure Material:	Thermoplastic polyester (PBT)
Frequency (f):	50 Hz
Function:	Surface socket outlet
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#216RS4W
Number of Poles:	2
Object Classification Code:	2CMT005069
Product Main Type:	TRS
Product Name:	Industrial Socket Outlet
Protection Type:	Watertight
Rated Current (I _n):	16 A
Rated Voltage (U _r):	100 ... 130 V 100 ⚡ 130 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Surface Socket Outlets

Suitable for Product Class: Industrial Plugs and Sockets

Classifications

E-nummer: 2416523

UNSPSC: 39120000

