



Datasheet for part number KJL7T11B35PN

| |
|---|
| Our Catalog Part Number: KJL7T11B35PN |
| Our Global Manufacturing Part Number: 111099-0003 |
| Brand: Cannon Product Category: Circular Product Line: 38999 Series I, II, and III Series: KJ |

| | |
|-----------------------------------|--|
| Product Datasheet | |
| SERIES | MIL - DTL - 38999 Series I |
| STYLE | Jam nut receptacle |
| CLASS | Environment resistant (without rear accessory) |
| SHELL SIZE | 11 |
| SHELL MATERIAL | Corrosion resistant shells of aluminum alloy |
| INSULATOR MATERIAL | High grade plastic |
| GROMMET AND SEAL MATERIAL | Silicone base elastomer |
| PLATING | Olive drab cadmium over electroless nickel plate |
| ARRANGEMENT | 11-35 |
| NUMBER OF CONTACTS | 13 contacts size 22D |
| GENDER | Pin |
| CONTACT TYPE | Rear release crimp snap-in contacts |
| CONTACT MATERIAL | Copper Alloy, gold plate |
| POLARIZATION | 95° |
| LOW PROFILE / LIGHT WEIGHT | no |
| SCOOP PROOF | yes |
| COUPLING SYSTEM | Bayonet |
| ELECTROLYTIC EROSION | no |
| DURABILITY (CYCLES) | 500 |
| HIGH IMPACT SHOCK | yes |
| EXTERNAL BENDING MOMENT (Size 25) | 650 in/lbs |
| RANDOM VIBRATION "J" | Ambient |
| SINE VIBRATION | 30 G, Ambient |
| SAND, DUST, ICE | yes |
| TEMPERATURE RANGE | 65°C (85°F) to + 175°C (+347°F) |
| CORROSION RESISTANT | 500 hours |
| TEST SERVICE RATING (MATED) | Sea Level = 1300 50000 ft. = 800 70000 ft. = 800 100000 ft. = 800 |
| TEST SERVICE RATING (UNMATED) | Sea Level = 1300 50000 ft. = 550 70000 ft. = 350 100000 ft. = 200 |
| OPERATING VOLTAGE | Vrms = 433 Vdc = 613 |