


Stainless steel

Terminal boxes KL



Material:
Stainless steel 1.4301
Enclosure: 1.25 mm
Cover: 1.25 mm

Surface finish:
Case and cover:
Brushed, grain 180

Protection category:
IP 66 to EN 60 529/10.91,
complies with NEMA 4x.

Supply includes:
Enclosure, cover with all-round
foamed-in PU seal and cover
screws, including plastic
bushes.

Approvals,
see page 23.

Detailed drawing,
see page 1119.

Width (B1) in mm	Packs of	150	300	200	300	400	300	Page
Height (H1) in mm		150	150	200	200	200	300	
Depth (T1) in mm		80	80	80	80	120	120	
Model No. KL	1	1521.010	1522.010	1523.010	1524.010	1525.010	1526.010	
Weight (kg)		1.3	1.8	1.8	2.4	3.6	3.9	
Cover screws		4	4	4	4	4	4	

Accessories

Mounting plate	1	1560.700	1561.700	1562.700	1563.700	1564.700	1567.700	909
Wall mounting bracket	4	1594.000	1594.000	1594.000	1594.000	1594.000	1594.000	905
Wall angle	1	2583.000	2583.000	2583.000	2583.000	2583.000	2583.000	906
Pole clamp	1	2584.000	2584.000	2584.000	2584.000	2584.000	2584.000	906
Support rails TS 35/7.5	10	2314.000	2316.000	2315.000	2316.000	2317.000	2316.000	927

To order terminal boxes in 1.4404 (AISI 316L), please add extension .510 to the Model No. Delivery times available on request.



Wall mounting bracket
for secure attachment to the
wall.
Model No. see page 905.



Housing coupling
for attaching the 120 mm deep
KL to the support arm system.
Model No. see page 278.