


# Terminal boxes KL

without gland plate, depth: 80



**Material:**

Enclosure: Sheet steel 1.25 mm  
Cover: Sheet steel 1.25 mm

**Surface finish:**

Case and cover:  
Dipcoat-primed,  
powder-coated on the outside  
in textured RAL 7035

**Protection category:**

IP 66 to EN 60 529/10.91,  
Complies with NEMA 4.

**Supply includes:**

Enclosure, cover with all-round  
foamed-in PU seal and cover  
screws, including plastic  
bushes.

**Approvals,**  
see page 23.

**Detailed drawing,**  
see page 1081.

Terminal boxes KL  
1.1

Width (B1) in mm	Packs of	150	200	200	300	300	400	600	Page
Height (H1) in mm		150	150	200	150	200	200	200	
Depth (T1) in mm		80	80	80	80	80	80	80	
<b>Model No. KL</b>	1	<b>1514.510</b>	<b>1528.510</b>	<b>1516.510</b>	<b>1515.510</b>	<b>1517.510</b>	<b>1518.510</b>	<b>1519.510</b>	
Weight (kg)		1.4	1.6	1.9	2.1	2.6	3.2	4.6	
<b>Accessories</b>									
Mounting plate	1	1560.700	1575.700	1562.700	1561.700	1563.700	1564.700	1566.700	909
Support rail TS 35/7.5	10	2314.000	2315.000	2315.000	2316.000	2316.000	2317.000	-	927
Support rail TS 35/15	10	-	-	-	-	-	-	2319.000	927
Cover retainer	3 pairs	1591.000	1591.000	1591.000	1591.000	1591.000	1591.000	1591.000	-
Cover hinge	6	1592.000	1592.000	1592.000	1592.000	1592.000	1592.000	1592.000	894

To order terminal boxes in textured RAL 7032 please add extension .210 to the Model No., and for primed terminal boxes use extension .310. Delivery times available on request.



**Double-membrane gland, stepped collar** for cable entry, Model No. see page 973.



**Cover retainer**  
The cover retainer KL 1591.000 is easily fitted without drilling, and allows the covers to be opened upwards, even when the terminal box below is bayed.