

HDS110
305211

Free to Air HD Satellite Receiver

- Free to Air Satellite HD/SD
- HDMI and SCART Outputs
- Dolby Digital Plus
- PVR Ready - Record, Pause and Rewind Live TV via an external HDD*
- Multimedia Player - Playback movies, music and photos via an external HDD*
- Front panel LED display
- Stores up to 4000 channels
- HDMI Lead included

* HDD not included

Technical Specifications

ORDER INFORMATION

EAN Number 5702663052116

CHARACTERISTICS

| | |
|-------------------------------|---|
| LNB voltage - Vertical | 13 V/DC |
| LNB voltage - Horizontal | 18 V/DC |
| DiSEqC control | Yes |
| Video decoding | MPEG-2 mp@hl, MPEG-4 sp, divx13.11, 4.x, 6.x' Flv format, h.264, mp@hl, ap(81_3 m&mb) |
| Audio decoding | MPEG-1, MPEG-2 (layer 1/11), mp3, acc-1c |
| Audio output (left+right) | Phono x 2 |
| Digital audio output (S/PDIF) | Coaxial x1 |
| HDMI Version | Yes |

FREQUENCY

Satellite - frequency range 950-2150 MHz

OPERATIONAL

| | |
|--------------------------|---------------------------|
| Remote control | Yes |
| Remote control - battery | 2 x AAA included |
| Buttons | 3 |
| Buttons - power | Yes (Standby) |
| Buttons - channel | Yes (up and down) |
| Software update | Via USB |
| Certification | CE |
| AC Supply voltage | 220...240 / 50...60Hz VAC |

| | |
|--------------------------|-----------|
| Power Consumption (typ.) | 10 max. W |
| User guide | Yes |

CONNECTORS

| | |
|--------------------------------|-------------------------|
| USB port | Yes |
| Single Cable/ SatCR / Unicable | Yes |
| Satellite - input connector | 'F' Female (IEC 169-24) |
| Connector HDMI | HDMI female (Type A) |
| Connector SCART | SCART in/out |
| TV Scart | Yes |
| IF input/loop out | Yes |

MECHANICAL

| | |
|------------------|---------------------|
| Display | LED |
| Display segments | 4 Digit / 8 Segment |
| Display colour | Blue |
| Colour | Black |
| Height (mm) | 35 mm |
| Depth (mm) | 135 mm |
| Width (mm) | 235 mm |
| Packaging Volume | 0,000 m3 |
| Net Weight | 0,730 kg |
| Tara Weight | 0,185 kg |
| Total Weight | 0,915 kg |
| Packaging Height | 0,000 m |
| Packaging Width | 0,000 m |
| Packaging Depth | 0,000 m |