


YOUR BEST SHOTS

Trendy camera phone equipped with 2 powerful cameras in a slim smooth body



VARIETY OF COLORS



black

golden

silver

rose gold



- Clear images even in low-light conditions: with 13.0MP rear camera with triple-LED flash, f/2.0 aperture and sensitive Samsung sensor
- Quality video calls & selfies: 8.0MP front camera with flash
- Exquisite body structure: slim metallized body (only 8.3mm) together with 2.5D curved screen glass ensure smooth and elegant, yet robust appearance
- Trendy color choice: smartphone comes in rose gold, golden, silver and black colors

- Lifelike content: high-precision 5.3" HD screen displays colors with great clarity
- High performance multitasking and energy saving: based on quad core processor and 1GB RAM
- Updated Android OS version: 6.0 Marshmallow version with smart battery saving mode Doze and lots of other up-to-date features
- Dual SIM: for optimizing budget on calls and Internet



SIM card slot	Dual SIM: WCDMA + GSM	Network	3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900 MHz
Display	Size: 5.3" Resolution: HD (720 x 1280) Technology: IPS, On-cell, 2.5D glass	Connectivity	BT 4.0+HS, Wi-Fi: 802.11b g n USB: microUSB 2.0
Processor	MT6580A 1.3 GHz Quad core	Audio	Mic, speakers, 3.5 jack
Memory	Built-in: 1 GB RAM + 8 GB eMMC Expandable: slot for microSD™ card up to 32GB	Built-in devices	GPS, FM
Power	2600 mAh Lion-Battery	Dimensions	146 x 73 x 8.3 mm
OS	Android 6.0 Marshmallow	Weight	156g (with battery)
Imaging	Front: 8.0MP FF with LED flash Rear: 13.0MP AF with triple-LED flash, f/2.0 aperture, Samsung sensor	In the box	USB cable, AC charger