



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	20 A
System Voltage	120 V AC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	Not rated
Electrical Connection	Pressure plate
Options	None

### Complementary

Short Circuit Current Rating	10 kA
Number of Spaces	1
Wire Size	AWG 14...AWG 8 (copper or aluminium)

### Environment

Certifications	UL listed CSA
Ambient air temperature for operation	104 °F (40 °C)

### Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901368717
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5300000000000003

Returnability	Y
Country of origin	MX

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1340 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Available

**Contractual warranty**

Warranty period	18 months
-----------------	-----------