



### Main

Product	Miniature circuit-breaker
Range	QO
Line Rated Current	40 A
System Voltage	120/240 V AC
Mounting Type	Bolt-on
Number of Poles	1P
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Options	None

### Complementary

Short Circuit Current Rating	10 kA
Number of Spaces	1
Wire Size	AWG 8...AWG 2 (copper or aluminium)

### Environment

Certifications	CSA UL listed
Ambient air temperature for operation	104 °F (40 °C)

### Ordering and shipping details

Category	00015 - QOB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901416784
Nbr. of units in pkg.	1
Package weight(Lbs)	0.31

Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1323 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------