

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370088](#)
Status: **Active**
Overview: [Outlet Boxes](#)
Description: Super-Safeway® Multiple Outlet Box, Standard Depth, 2-Sided, NEMA 5-15 Duplex Receptacles, Cord Clamp, Duplex Cover Plates

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating N/A
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Outlet Boxes](#)
 Product Name Super-Safeway™
 Receptacle Type Duplex
 Type Multiple Outlet Box
 UPC 78678874150
 Woodhead Yes

Physical

Cord Diameter 8.26-16.64mm (.325-.655")
 Cord Grip Body Size Double C-Clamp
 Cord Length N/A
 Feed-Thru No
 Flip Lid No
 Material - Housing Rubber
 Number of Receptacles 2
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 3000-1

Reference - Drawing Numbers

Sales Drawing SD-130137-031



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[130137](#) Series