

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530028](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Safeway® In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, Molded NEMA 5-15 Tri-Tap, 15A, 120V, 0.61m (2.0') Cord Length

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)  
[Product Literature \(PDF\)](#)

**Agency Certification**

CSA      LR6837  
 UL      E66308

**General**

Product Family      Power Distribution  
 Series      [130153](#)  
 Enclosure Rating      NEMA 4  
 GFCI Reset      Manual  
 Mounting Style      Portable  
 Open Neutral Relay      Yes  
 Overview      [Ground Fault Circuit Interrupter \(GFCI\) Products](#)  
 Product Literature Order No      987650-7737, 987651-0452  
 Product Name      Safeway®  
 Receptacle Type      N/A  
 Type      GFCI Commercial Duty, Single Phase  
 UPC      78678828428  
 Woodhead      Yes

**Physical**

Cord Diameter      10.92mm (.430")  
 Cord Grip Body Size      Internal Double C-Clamp  
 Cord Length      0.61m (2.0')  
 Feed-Thru      Yes  
 Flip Lid      No  
 Material - Housing      Nylon  
 Net Weight      566.990/g  
 Number of Receptacles      3  
 Packaging Type      Bag

**Electrical**

Cord Type      N/A  
 Current - Maximum per Contact      15.0A  
 GFCI      Yes-In-line  
 Ground Continuity Monitor      No  
 NEMA Configuration      NEMA 5-15  
 Voltage - Maximum      120V AC

**Material Info**

Engineering Number      15050-3TT



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[130153 Series](#)